

Installation Instructions

Access 7 A

Tehonsyöttö:
8...30 VDC 100 mA

Kytkenä:

24VDC	Punainen
MAA	Musta
Wie 0 (Data)	Vihreä
Wie 1 (Clock)	Valkoinen
RxD	Harmaa
TxD	Pinkki
Mode	Violetti
Summeri	Keltainen
Vihreä LED	Sininen
Punainen LED	Ruskea

Jos lukijaa käytetään clock&data moodissa, kytke Mode- johdin MAA-johtimeen. Wiegand- moodissa Mode- johdinta ei kytketä.

Lukijoiden sijoittaminen alle 10 cm etäisyydelle toisistaan tai lukijan asentaminen metallipinnalle saattaa lyhentää lukuetaisyyttä.

Älä asenna voimakkaiden sähköhäiriölähteiden läheisyyteen.

Älä katkaise kaapelia alle 10 cm pituiseksi.

Idesco Oy vakuuttaa täten, että Access 7 A lukija on direktiivin 1999/5/EY oleellisten vaatimusten ja sitä koskevien direktiivin muiden ehtojen mukainen.

Power supply:
8...30 VDC 100 mA

Connection:

24VDC	Red
GND	Black
Wie 0 (Data)	Green
Wie 1 (Clock)	White
RxD	Gray
TxD	Pink
Mode	Violet
Buzzer	Yellow
Green LED	Blue
Red LED	Brown

Connect Mode to GND if reader is to be used in clock&data operation. Mode is not connected in Wiegand operation.


If readers are placed closer than 10 cm distance from each other or if the reader is installed on metal the reading distance can be shorter.

Do not install close to sources of powerful electromagnetic disturbance.

Do not cut the cable shorter than 10 cm.

Hereby, Idesco Oy, declares that this Access 7 A reader is in compliance with the essential requirements and other relevant provisions of directive 1999/5/EC.

Access housing



Access Quattro housing

